

# AJ CHAIR


## Design brings comfort

UCHIDA

The resin mesh which shape can change flexibly not only easily fit the users' back but also gives support. What AJ looks for is a design which brings comfort to the users. Reclining includes synchro type and auto-sensing mechanism type. The chair in new shape looks for bringing comfort to the users all the time.



### POINT



#### ■ The comfort of Polyamide 3D Mesh

The leaning back in polyamide 3D mesh is consisted by stitches in difference size in every area. It is freely adjustable to fit with the users' backs and brings the most comfortable sitting mood to the users as well. It provides good support to the users' back even though he / she sit for a long time.



#### ■ Following users' movement to bring their backs comfort

The upper part of the leaning back is in good structure. The shape can change flexibly to match with users' movement and the change of postures. No matter leaning back, stretching or turning around, there will have no stress at all.

### 2 Types of Reclining Function for Choice


#### Synchro-Reclining Type (+ Adjustable function of seat depth)

#### ■ Comfort by users' adjustment

Apart from reclining, you can also hold the leaning back at your preferred angle by the one-touch function.










#### Auto-sensing (Weight Sensing) Type



#### ■ Comfort by reducing the adjustment

The reclining strength that responds to users' physiques and postures and the strength adjustment can provide the perfect sitting mood to the users.

Specification

		Synchro-Reclining Type (+ Adjustable function of seat depth)		Auto-sensing Mechanism (Weight Sensing) Type	
		Fully Adjustable Armrest	Without Armrest	Fully Adjustable Armrest	Without Armrest
		Armrest			
Leg					
Resin	Nylon Caster	Model Number Item Name 1-5-347-420□-00 AJS-320BN-PA	1-5-347-400□-00 AJS-300BN-PA	1-5-347-320□-00 AJA-320BN-PA	1-5-347-300□-00 AJA-300BN-PA
	Urethane Caster	Model Number Item Name 1-5-347-470□-00 AJS-320BN-PU	1-5-347-450□-00 AJS-300BN-PU	1-5-347-370□-00 AJA-320BN-PU	1-5-347-350□-00 AJA-300BN-PU

**Back Resin Mesh**  
 •PA (Polyamide)  
 Resin Molded Products



Please assign the □ number to choose color

Seats Upholstery  
 •Polyester 100%

				
0 Black	1 Grey	4 Blue	6 Green	8 Red

Option

Armrest



AJ Adjustable Armrest UHB Type  
 1-5-347-0905-00

Caster



Nylon Caster

Urethane Caster

▶Nylon caster can be chosen for carpeted floor or if the floor is not slippery like soft or with cushion. Otherwise, please choose urethane caster (sold separately) if it is a hard floor like wooden flooring or if dirt is a concern to the users.

■ AJ Specification

Structure	Reclining Shape	Synchro-type / Synchro-Reclining of the seat and the back Auto-sensing Type / Reclining Back
	Reclining Mechanism	Synchro-type / Free Reclining, Adjustment of Reclining Angle (3 Stages), Adjustment of Reclining Strength Auto-sensing Type / Free Reclining, stopping at Front & Back
Materials	Up & Down Adjustment for the seats and backs / Tackling structure	Gas-style up & down adjustment for the seats and backs / Seats Tackling
	Seats	Cushion / Mold Urethane
	Back's Mesh / Back's Frame	Polyamide / Reinforced Plastic (Polyamide)
	Armrest	Main body / Reinforced Plastic, Arm pad / Urethane
	Legs	Resin Legs / Reinforced Plastic (Polyamide)
	Caster	Nylon Caster, Urethane Caster

UCHIDA YOKO GLOBAL LIMITED

Hong Kong Headquarters

Unit 3, 9/F, AXA Centre, 151 Gloucester Road,  
 Wan Chai, Hong Kong  
 Tel:+852-2877-3663 Fax:+852-2877-3132

Tokyo Branch

Uchida Yoko Shinkawa No.2 Bldg.3F, 2-3-9 Shinkawa,  
 Chuo-ku, Tokyo 104-0033  
 Tel:+81-3-3555-4781 Fax:+81-3-3555-6423/6424

Email:sales@uchidayoko.com  
 http://www.uchidayoko.com http://www.uchida.co.jp